

OUR REF: TAP/06/2025/ HIMSA II K/S**ENQ: SHELEEN KAVIKAIRIUA**17th June 2025**MR. SAM SHIVUTE**Commissioner
Namibia Revenue Agency
Moltke Street, Windhoek
Namibia**PER EMAIL:**Johanna.Amukushu@namra.org.na

Dear Custom Officials,

TYPE APPROVAL EXEMPTION – HIMSA II K/S

Kindly note that the Authority has reviewed the documentation describing equipment to be imported into Namibia by HIMSA II K/S and hereby confirms that the following model: Noahlink Wireless 2 does not require type approval.

This letter therefore, serves only as an exemption for the equipment mentioned above and may not be used for other consignments without the consent of the Authority.

In light of trade facilitation, the Authority thus requests Customs to please allow the equipment to pass the border as they do not require Type Approval.

For any further information or clarity please do not hesitate to contact Ms. Sheleen Kavikairiua, Manager: Licensing Standards & Regulatory Compliance, at Tel: 061 222 666 or via email: skavikairiua@cran.na

Yours faithfully,


MRS. EMILIA NGHIKEMBUA
CHIEF EXECUTIVE OFFICER

Specifications

Noahlink))) Wireless 2

Intended Use:

Noahlink Wireless 2 is intended to enable a hearing instrument fitter to wirelessly adjust the settings of wireless hearing instruments. The primary function of the Noahlink Wireless 2 programming interface is to transfer information signals between a PC installed with fitting software and wireless hearing instruments.

List of Countries:

Noahlink Wireless 2 is a communications device, and will conform to the essential requirements and other relevant provisions in over 20 regions and countries:

The declaration of conformity for these countries will be available in the *Noahlink Wireless 2 Certificates and Approvals* at www.himsa.com as soon as they are ready.

Technical Specifications:

Operating range:	3 meters
Bluetooth Version:	BLE 5.3
Wireless (2.4 GHz):	BT LE: 2402-2483 MHz
Modulations:	GFSK
Number of channels:	40
Data rate:	1 Mbps / 2 Mbps
Output power:	+9 dBm EIRP
Antenna:	Internal antenna, Gain: 3dBi
Operating temperature:	0°C to 55°C (32°F - 131°F)
Storage temperature:	-20°C to 60°C (-4°F - 140°F)
Power supply:	Powered by the USB port of a PC
Operating Voltage:	5 VDC
BT Chipset:	Manufacturer: Nordic Semiconductor, Model: nRF5340

<https://www.nordicsemi.com/products/nrf5340>

Temperature test, transport and storage information

The product is subjected to various tests in temperature and damp heating cycling between -25 C and +70 C according to internal and industry standards.

Warranty:

The Noahlink Wireless 2 programming interface is covered by a limited warranty issued by the manufacturer for a period of 12 months from the date of original purchase. Please notice that extended warranties may apply in your country. Please contact your local hearing instrument manufacturer. Be aware of information marked with the warning symbol.

For More Information:

Please refer to the Noahlink Wireless 2 User Manual, found in the *Noahlink Wireless Knowledgebase* at www.himsa.com.

CPD-2 External photos



Hearing Instrument
Manufacturers'
Software Association

